



## Flat clamp, Slot width a: 14mm



### Order data

Order number	375115 14
GTIN	4020772374150
Item class	35A

### Description

#### Version:

Low design, position the flat clamp on the workpiece. Then tighten the securing screws for the machine table. The workpiece is clamped by turning the clamping screw.

#### Application:

**For lateral clamping of especially thin components**, in order to perform complete machining operations without interference contours. Can be used both horizontally and vertically.

#### Material:

Hardened steel, burnished finish.

### Technical description

Thread G	M12
Minimum height $h_1$	16 mm
Maximum height $h_2$	25 mm
Clamping force $F_2$ vertical	7.5 kN
Slot width a	14 mm
Intermediate height $H_1$	16 mm
Clamping force $F_1$ horizontal	15 kN
Length L	110 mm
Width B	44 mm

Type	6496
Type of product	Side clamps