



HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7 (mm or inch): 13,8



Order data

Order number	122507 13,8
GTIN	4045197832627
Item class	12F

Description

Version:

Straight major cutting edges and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Standard: DIN 6537 K

Tolerance nominal \varnothing : h7

Number of cutting edges Z: 2

Tolerance nominal \varnothing : h7

recommended maximum drilling depth L_2 : 39.3 mm

Overall length L: 107 mm

Shank $\varnothing D_s$: 14 mm

Feed f in steel < 900 N/mm²: 0.26 mm/rev.

Technical description

Flute length L_c	60 mm
recommended maximum drilling depth L_2	39.3 mm
Number of cutting edges Z	2
Overall length L	107 mm
Feed f in steel < 900 N/mm ²	0.26 mm/rev.

Tolerance nominal \varnothing	h7
Nominal $\varnothing D_c$	13.8 mm
Standard	DIN 6537 K
Shank $\varnothing D_s$	14 mm
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140°
Shank	DIN 6535 HB to h6
Through-coolant	yes, to 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm ²	suitable	125 m/min	P
Steel < 750 N/mm ²	suitable	115 m/min	P
Steel < 900 N/mm ²	suitable	95 m/min	P
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	65 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M

INOX > 900 N/mm ²	suitable only under restricted conditions	30 m/min	M
GG	suitable	100 m/min	K
GGG	suitable	65 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		