

Garant**CC.T 060204, Grade: HB7120-1**

Order data

Order number	260142 HB7120-1
GTIN	4045197817174
Item class	21G

Description

CC.T 060204 HB7120-1 Grade: HB7120-1
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.2 - 4 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 80 - 260 m/min

Technical description

Main application	M
Corner radius	0.4 mm
Cutting conditions	continuous
Cutting speed v_c main application	80 - 260 m/min
Grade	HB7120-1
Chip breaker	VM

Cutting depth a_p	0.2 - 4 mm
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CCMT 060204
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning