

Garant**CC.T 09T304, Grade: HB7120-1**

Order data

Order number	260150 HB7120-1
GTIN	4045197817198
Item class	21G

Description

CC.T 09T304 HB7120-1 Grade: HB7120-1
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.2 - 4 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 80 - 260 m/min

Technical description

Main application	M
Chip breaker	VM
Corner radius	0.4 mm
Grade	HB7120-1
Cutting speed v_c main application	80 - 260 m/min
Feed f	0.1 - 0.4 mm/rev.

Cutting conditions	continuous
Cutting depth a_p	0.2 - 4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CCMT 09T304
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning