

PLANOLITH**Universal precision comparator stand with 3-D NOGA jointed arm, Table length×Width: 400X250mm****Order data**

Order number	442525 400X250
GTIN	2050001055408
Item class	46H

Description**Version:**

Precision diamond lapped table, with test certificate. Solid 3D jointed arm with mechanical central clamping. Continuously adjustable clamping force with high stability. Quick and easy positioning. Universal indicator holder.

With fine adjustment, for clamping shank \varnothing 8 mm, \varnothing 6 mm, \varnothing 3/8 inch and indicators with dovetail clamping shanks.

Technical description

Length of jointed arm L_2	113 mm
Weight	17.5 kg
Length of jointed arm L_1	133 mm
Connection thread	M8
Action radius of 3-D jointed arm	290 mm
Standard	DIN 876/1

Test certificate	Manufacturer's test certificate
Calibration	D1
Type of product	Comparator stand

Services

CalibrationComparator stand maximum table size 400X400 mm	024580 400X400
--	----------------

Accessories

3-D jointed arm Type 240	442114 240
3-D jointed arm Type 240	442110 240
3-D jointed arm Type 290	442114 290
3-D jointed arm Type 290	442110 290
Holder for measuring stand Type 2SM	442100 2SM