

Mitutoyo**Precision vernier height gauge, Marking height: 300mm****Order data**

Order number	443500 300
GTIN	4946368096223
Item class	44A

Description**Version:**

Sturdy base with ground base, **scale hardened and ground**.

All reading parts are anti-glare satin chrome-plated. Sharp jet black scales. With fine adjustment. Slightly raised edges to the scale prevent the slide from damaging it. Reading zero and marking scribe are adjusted with reference to the bottom of the base (marking out from "0"). Drawing dimensions can therefore be transferred directly without the risk of calculation errors.

The scribe is **carbide tipped**. With adjustable measuring beam.

Technical description

Marking height	300 mm
Column cross section	28×9 mm
Calibration	E1
Base length	135 mm
Base width	91 mm
Vernier	1/50 mm

Error limit	0.04 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum measuring range 300 mm	024630 300
DAkkS calibrationHeight gauge / height scriber maximum measuring range 300 mm	024640 300

Accessories

Spare scriber, carbide tipped for marking heights 300 mm	443510 300
--	------------