



Bench centre with ground measuring faces, without dial indicator, Tip height: 50mm



Order data

Order number	443000 50
GTIN	4030234000169
Item class	46K

Description

Version:**Measuring stand:**

With fine setting adjustment and holder bore 8 H7. The cross arm is full adjustable for height and in all lateral directions.

Tailstocks:

adjustable. Left tailstock with fixed centre, right tailstock with axially movable quill.

Measuring bench:

Precision ground, with 2 T-slots. To take the tailstocks (tolerance H7) or the stand.

Flatness to DIN 876/1.**Application:**

For measuring round and plane accuracy as well as for comparative tests of parallelism and diameter.

Supplied with:

Bench, measuring stand. Tailstocks without Vee blocks.

Technical description

Footprint length	350 mm
Cross arm length	60 mm
Column Ø	16 mm

Baseplate width	100 mm
Lateral and vertical alignment of tailstocks	±0.01 mm
Weight	8 kg
Tip height	50 mm
overall height without stand	110 mm
T-slot width H7	10 mm
Cross arm Ø	16 mm
Centre Ø	16 mm
Pillar height	150 mm
Maximum clear span between centres	200 mm
Calibration	Price on request
maximum load capacity per pair	10 kg
Type of product	Radial and axial run-out tester

Accessories

Pair of bench inspection rollers height adjustable for maximum workpiece Ø 32 mm	443050 32
Pair of bench inspection rollers for tip height 50/75 mm	443160 50/75
Jointed stand with T-nut Throat 200 mm	443295 200
Jointed stand with T-nut Throat 130 mm	443295 130