



## HOLEX Pro Steel solid carbide drill, Whistle-Notch shank DIN 6535 HE, TiAlN, Ø DC h7 (mm or inch): 5,5



### Order data

Order number	122503 5,5
GTIN	4045197834423
Item class	12F

### Description

#### Version:

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Machining strategy: HPC

Standard: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

recommended maximum drilling depth  $L_2$ : 19.8 mm

Overall length L: 66 mm

Shank Ø  $D_s$ : 6 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.14 mm/rev.

### Technical description

Nominal Ø $D_c$	5.5 mm
Number of cutting edges Z	2
Flute length $L_c$	28 mm
Shank Ø $D_s$	6 mm
Feed f in steel < 900 N/mm <sup>2</sup>	0.14 mm/rev.

Tolerance nominal $\varnothing$	h7
Overall length L	66 mm
recommended maximum drilling depth L <sub>2</sub>	19.8 mm
Standard	DIN 6537 K
Coating	TiAlN
Tool material	Solid carbide
Version	4×D
Point angle	140 °
Shank	DIN 6535 HE to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
wet maximum	suitable		
dry	suitable		

