

**HAFF &  
SCHNEIDER**

### 3D edge finder, analogue, with contact point (Ø 4 mm)



#### Order data

Order number	359550
GTIN	2050001659224
Item class	36T

#### Description

##### Version:

- **Linear scale.**
- **Suitable for measuring.**
- **Precise operation.**
- **Compact design avoids collisions when finding edges.**
- **Dust-tight and watertight = IP67.**
- **Convenient and exact concentricity adjustment.**
- **One scale for both radial and axial run-out.**

##### Version of the advertising text:

- **With linear scale.**
- **Convenient and exact concentricity adjustment.**

##### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

##### Application:

Precision measuring device for milling and spark erosion machines. For determining component zero-points, measurement of lengths, bore centres and reference edges.

##### Supplied with:

With contact point No. 359505 size 4.

##### Optional extras:

Contact point No. 359505 size 6.

**Note:**

Digital 3D edge finder No. 359500.

Suitable contact points No. 359505 and spare glass No. 359510.

## Technical description

Displacement travel x, y, z respectively	7 mm
free length contact point	40 mm
Spare contact point	359505 4
Measuring accuracy	0.01 mm
Display Ø	50 mm
Overall length (body and contact point)	134 mm
Reading accuracy	0.01 mm
Spare glass	359510
Shank Ø	16 mm
Shaft length	40 mm
IP Index of Protection	IP 67
Type of product	Probes

## Accessories

Spare glass for analogue 3D edge finder	359510
Side lock arborForm AD Clamping range Ø D1 16 mm	300410 16
Contact point for 3D edge finder Spherical point Ø D 4 mm	359505 4
Contact point for 3D edge finder Spherical point Ø D 6 mm	359505 6
Bellows for 3D edge finder	359512