

**Stock square Accuracy class 2, Stock length: 400X200mm****Order data**

Order number	452590 400X200
GTIN	4045197372178
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Shank cross-section	35×7 mm
Right angle tolerance	0.06 mm
Stock length	400×200 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Stock square

ServicesCalibrationStock, try, and bevel edge squares maximum
arm length 750 mm

025000 750

DAkkS calibrationStock, try, and bevel edge squares
maximum arm length 750 mm

025010 750