



HOLEX Pro Steel solid carbide drill, Whistle-Notch shank DIN 6535 HE, TiAlN, Ø DC h7 (mm or inch): 10,7



Order data

Order number	122503 10,7
GTIN	4045197834942
Item class	12F

Description

Version:

Straight major cutting edges and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Machining strategy: HPC

Standard: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 39 mm

Overall length L: 102 mm

Shank Ø D_s : 12 mm

Feed f in steel < 900 N/mm²: 0.22 mm/rev.

Technical description

Tolerance nominal Ø	h7
Overall length L	102 mm
Standard	DIN 6537 K
Shank Ø D_s	12 mm
recommended maximum drilling depth L_2	39 mm

Nominal $\varnothing D_c$	10.7 mm
Feed f in steel < 900 N/mm ²	0.22 mm/rev.
Number of cutting edges Z	2
Flute length L _c	55 mm
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140°
Shank	DIN 6535 HE to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	115 m/min	P
Steel < 750 N/mm ²	suitable	105 m/min	P
Steel < 900 N/mm ²	suitable	85 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
INOX < 900 N/mm ²	suitable	30 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
wet maximum	suitable		
dry	suitable		

