

Garant**Parallel clamping jaw, Jaw width: 48mm****Order data**

Order number	360085 48
GTIN	4045197482419
Item class	310

Description**Application:**

Variable pitches can be achieved using crossed clamping rails.

Suitable for:

Clamping rail No. 360080.

Note:

For use with clamping rails from revision 3 onwards (see illustration). Attachment bar on multi-point clamping rails must not be wider than 5 mm.

Technical description

Jaw width	48 mm
Torque	5 Nm
Torque	10 Nm
Torque	15 Nm
Torque	20 Nm
Clamping force	5 kN
Clamping force	10 kN
Clamping force	15 kN

Clamping force	20 kN
max. stroke	3 mm
T-bolt AF	5 mm
Shank screw AF ₁	4 mm
Type of product	Vice jaws