

 Mahr**Micrometer with dial comparator, Measuring range: 150-200mm****Order data**

Order number	424800 150-200
GTIN	2050001036674
Item class	43A

**Description****Version:**

Measuring spindle of stainless steel, hardened and ground. Carbide-tipped measuring faces. Controls and reading parts satin chrome-plated. With hand temperature protection. Constant measuring force. Moveable stop anvil, retractable. Particularly suitable for series manufactured parts.

**Accuracy:**

**Dial comparator DIN 863 – micrometer 2 µm.**

**Supplied with:**

Dial comparator Millimes No. 434674 size 50/1.

**Technical description**

Graduation of the micrometer	0.01 mm
Barrel Ø	18 mm
Spindle Ø	7.5 mm
Measuring range dial comparator	±0.05 mm
Measuring range	150 - 200 mm
Graduation of the precision dial comparator	0.001 mm

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B14
Type of product	Micrometer with dial comparator

### Services

CalibrationMicrometer with dial comparator maximum measuring range 200 mm	022400 200
DAkkS calibrationMicrometer with dial comparator maximum measuring range 200 mm	022410 200

### Accessories

Precision dial comparator $\pm$ measuring range / reading 50/1 $\mu$ m	434674 50/1
--	-------------