

 Mahr**Precision bench micrometer, Measuring range: 0-50mm****Order data**

Order number	424805 0-50
GTIN	4059192004774
Item class	43A

Description**Version:**

Strong steel frame, can be inclined up to 45° against sturdy base. Height-adjustable stop. Measuring spindle of stainless steel, hardened and ground. Carbide-tipped measuring faces. Controls and reading parts satin chrome-plated. With hand temperature protection. Constant measuring force. Moveable stop anvil; lifting with retraction lever. Especially suitable for series manufactured parts and quick inspection.

Accuracy:

Dial comparator DIN 863 – micrometer 2 µm.

Supplied with:

Dial comparator Millimes No. 434674 size 50/1.

Technical description

Graduation of the micrometer	0.005 mm
Measuring range	0 - 50 mm
Barrel Ø	25 mm
Spindle Ø	7.5 mm
Measuring range dial comparator	±0.05 mm

Graduation of the precision dial comparator	0.001 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B14
Type of product	Micrometer with dial comparator

Services

DAkkS calibrationMicrometer with dial comparator maximum measuring range 100 mm	022410 100
CalibrationMicrometer with dial comparator maximum measuring range 100 mm	022400 100

Accessories

Precision dial comparator \pm measuring range / reading 50/1 μm	434674 50/1
---	-------------