



Micrometer with dial comparator, Measuring range: 25-50mm



Order data

Order number	422500 25-50
GTIN	4059192004255
Item class	43A

Description

Version:

Measuring spindle through hardened and ground.

With precision lapped **carbide tipped anvils**.

Spindle and anvil of stainless steel.

One piece frame and spindle guide.

Button for retracting the measurement anvil for repetitive measurements.

With adjustment screw for zeroing.

Tolerance pointers for good/ reject measurements.

With hand temperature protection. Lever for spindle clamping.

Callout:

Deviation read-off in 1/1000 mm.

Push button for anvil retraction.

Accuracy:

Dial comparator 1 μm – micrometer 2 μm .

Technical description

Measuring range dial comparator	± 0.065 mm
Graduation of the micrometer	0.01 mm
Measuring range	25 - 50 mm

Graduation of the precision dial comparator	0.001 mm
Clearance depth of micrometer frame	30 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B9
Type of product	Micrometer with dial comparator

Services

CalibrationIndicator micrometer maximum measuring range 200 mm	022100 200
--	------------