



## External micrometer with disc anvils, Measuring range: 100-125mm



### Order data

Order number	423000 100-125
GTIN	4045197204042
Item class	42B

### Description

#### Version:

With large-area, hardened disc anvils. Forged and enamelled frame.  
Design with rotating spindle.

#### Application:

For determining the tooth widths of spur and helical gears from module 0.8.

#### Supplied with:

From size 25-50 including 1 setting standard.

### Technical description

Disc anvil $\varnothing$	30 mm
Parallelism of the measuring faces	6 $\mu$ m
Micrometer barrel graduations	1/50 mm
Spindle pitch	0.5 mm
Measuring range	100 - 125 mm
Spindle $\varnothing$	8 mm
Scale divisions	0.01 mm
Calibration	B2
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External micrometer

## Services

Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200
DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200

## Accessories

Micrometer setting standard overall length 100 mm	421100 100
---	------------