

Garant
Stub drill HSS-E FS, uncoated, Ø DC h8: 8,1 mm


Order data

| | |
|--------------|---------------|
| Order number | 113020 8,1 |
| GTIN | 4045197002600 |
| Item class | 11B |

Description

Version:

Particularly **robust and strong** due to **strengthened core**.

Ground flutes, with high concentricity.

Bright finish flutes, nitrided lands.

With point geometry shape C up to 3.9 mm; shape S (special) from 4 mm.

Advantage:

Ideal for drilling shallow holes (approx. 2 - 4×D) on NC machines and automatic machines.

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Technical description

| | |
|--|-------------|
| Flute length L_c | 37 mm |
| Nominal $\varnothing D_c$ | 8.1 mm |
| Feed f in steel $< 750 \text{ N/mm}^2$ | 0.1 mm/rev. |
| Number of cutting edges Z | 2 |
| Tolerance nominal \varnothing | h8 |
| Shank $\varnothing D_s$ | 8.1 mm |
| Overall length L | 79 mm |
| Standard | DIN 1897 |
| recommended maximum drilling depth L_2 | 24.9 mm |
| Point angle | 135 degrees |

| | |
|-----------------|--------------|
| Shank | Plain shank |
| Coating | uncoated |
| Tool material | HSS E |
| Type | FS |
| Helix angle | 38 degrees |
| Through-coolant | no |
| Colour ring | without |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|-------------|----------------|----------|
| Alu plastics | suitable | 70 m/min | N |
| Aluminium (short chipping) | suitable | 45 m/min | N |
| Steel < 500 N/mm ² | suitable | 40 m/min | P |
| Steel < 750 N/mm ² | suitable | 30 m/min | P |
| GG(G) | suitable | 25 m/min | K |
| Oil | suitable | | |
| wet maximum | suitable | | |