

**Indicating snap gauge with handle Marameter S, Measuring range: 30-60mm****Order data**

Order number	424910 30-60
GTIN	2050001050984
Item class	43A

**Description****Version:**

Powerful, rigid frame with handle. Anvils made of stainless, hardened steel. **Anvils carbide tipped and chamfered at the front for easier insertion.** For measuring narrow registering edges that protrude beyond the frame. Setting by gauge blocks. Adjustable centring back-stop for setting component centre.

**High measuring accuracy.** Device weight rests on fixed anvil base during measuring and does not influence the measuring result.

**Constant measuring force** ensured by built-in measuring force spring. Can be used with all dial gauges (not included in the price) with 8 mm clamping shank. Dial comparator No. 434674 is preferred.

**Out-of-tolerance component values can be read numerically on the dial indicator.** Lateral frame projection to protect against shocks during measuring and when setting down.

**Callout:**

Adjustable fixed anvil.

Adjustable centring stop.

Anvil with redirection to dial indicator.

**Application:**

For measuring all kinds of cylindrical parts. As a quick measuring device directly on the machine tool and in production control.

**Supplied with:**

**Without** dial indicator, **with a** wooden box.

**Optional extras:**

Setting dimensions, gauge blocks, gauging discs, precision dial comparator No. 434674.

**Note:**

Measuring range up to 500 mm on request

---

**Technical description**

Plane parallelism of measuring faces	3 µm
Gauging force	13.5 N
Measuring face Ø	18 mm
Measuring range	30 - 60 mm
Flatness of measuring faces	0.5 µm
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Calibration	L9
Type of product	Indicating snap gauge

---

**Services**

Calibration Adjustable snap gauge Type RL	028730 RL
---	-----------