

**HOLEX**
**HOLEX Pro Steel solid carbide drill, Whistle-Notch shank DIN 6535 HE, TiAlN, Ø DC h7 (mm or inch): 5,7**

**Order data**

Order number	122508 5,7
GTIN	4045197835680
Item class	12F

**Description**
**Version:**

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Machining strategy: HPC

Standard: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

recommended maximum drilling depth  $L_2$ : 19.5 mm

Overall length L: 66 mm

Shank Ø  $D_s$ : 6 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.14 mm/rev.

**Technical description**

Standard	DIN 6537 K
Feed f in steel < 900 N/mm <sup>2</sup>	0.14 mm/rev.
recommended maximum drilling depth $L_2$	19.5 mm
Overall length L	66 mm
Flute length $L_c$	28 mm

Tolerance nominal $\varnothing$	h7
Shank $\varnothing D_s$	6 mm
Number of cutting edges Z	2
Nominal $\varnothing D_c$	5.7 mm
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140°
Shank	DIN 6535 HE to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Colour ring	green
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	125 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	95 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	65 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	M
GG	suitable	100 m/min	K
GGG	suitable	65 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		