

**Mitutoyo****Internal micrometer set Holtest for measuring blind holes, Measuring range: 12-20mm****Order data**

Order number	429055 12-20
GTIN	4946368517582
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. Blind hole version. **Measuring faces of hardened steel with titanium coating for long tool life.**

**Supplied with:**

Internal micrometers No. 429005. Setting rings similar to No. 484030, extension 150 mm No. 429010.

**Technical description**

Measuring range	12 - 20 mm
Number of micrometers	2
Setting ring $\varnothing$	16 mm
Error limit	0.004 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

## Services

CalibrationInternal micrometer set Measuring range 12-20 mm

020550 12-20

---

## Accessories

Setting ringDIN 2250 C Nominal size Ø 18 mm

484030 18

Internal micrometer Holtestfor measuring blind holes  
Measuring range 16-20 mm

429005 16-20

Internal micrometer Holtestfor measuring blind holes  
Measuring range 12-16 mm

429005 12-16

Extension for internal micrometer Type 2/150

429010 2/150

Setting ringDIN 2250 C Nominal size Ø 15 mm

484030 15