

Mitutoyo**Internal micrometer Holtest for measuring blind holes, Measuring range: 12-16mm****Order data**

Order number	429005 12-16
GTIN	4946368517186
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. Blind hole version. **Measuring faces of hardened steel with titanium coating for long tool life.**

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Measuring range	12 - 16 mm
Standard measuring depth	80 mm
Barrel Ø	23 mm
Overall length	127 mm
Dimension a	0.3 mm
Measuring depth with extension	230 mm
Error limit	0.004 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/429005-12-16>