



## Knurl forming tool right-hand, Shank size: 16mm



### Order data

Order number	290080 16
GTIN	4030741660986
Item class	29H

### Description

#### Version:

Grub screws in the shank for clearance angle correction.  
Carbide roller pin for increased wear resistance.

**Top face of the shank = tip height**

### Technical description

for knurl bore $\varnothing d_2$	6 mm
Working range	3 - 50 mm
for knurl width w	6 mm
Shank height	16 mm
Shank width	16 mm
for knurl $\varnothing d_1$	15 mm
for knurled countersunk $\varnothing d_3$	11 mm
Closure stud	299925 1
Disc	299927 1
for knurl profile	RAA 1×AA
Type of product	Self-centering knurling tool

---

**Accessories**

Disc Type 1	299927 1
Closure stud Type 1	299925 1