



Knurl forming tool right-hand, Shank size: 16mm



Order data

Order number	290094 16
GTIN	4030741498527
Item class	29H

Description

Version:

- **Minimal pressure reduces stress on the workpiece and machine.**
- **Synchronising spindle for easy adjustment of knurl carriers and centre heights.**

Grub screws in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Technical description

for knurl width w	6 mm
for knurl $\varnothing d_1$	15 mm
Shank height	16 mm
for knurl bore $\varnothing d_2$	6 mm
Shank width	16 mm
Working range	0 - 15 mm
for knurled countersunk $\varnothing d_3$	11 mm

Closure stud	299925 1
Disc	299927 1
Cutting direction	Left-hand and right-hand
for knurl profile	RAA 2×AA
Type of product	Self-centering knurling tool

Accessories

Disc Type 2	299927 2
Closure stud Type 2	299925 2