

**Garant**
**Vernier caliper, Measuring range: 150mm**

**Order data**

Order number	410100 150
GTIN	4045197502506
Item class	40Z

**Description**
**Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper.

Precision lapped measuring faces. Better reading due to a colour-contrast scale.

**Optional extras:**

Thread table No. 412180 for caliper back.

**Technical description**

Packaging	Wallet
Calibration	A1
Scale divisions	0.05 mm
Measuring range	0 - 150 mm
Jaw length	40 mm
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3

Depth gauge available	yes
Measurement deviation E MPE	$\pm 0.05$ mm
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

### Accessories

Synthetic leather case for vernier calipers	412500
---	--------