

Garant
Vernier caliper, Measuring range: 150 mm

Order data

Order number	410100 150
GTIN	4045197502506
Item class	40Z

Description
Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper.

Precision lapped measuring faces. Better reading due to a colour-contrast scale.

Thread table: Calipers table

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: flat

Packaging: Wallet

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Graduation: 1/128 in

Jaw length: 40 mm

Technical description

Packaging	Wallet
Calibration	A1
Scale divisions	0.05 mm
Measuring range	0 - 150 mm

Jaw length	40 mm
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	DIN 862
Depth gauge	flat
Depth gauge available	yes
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Plastic case Type MS150	412468 MS150
Plastic case Type MS150	412470 MS150
Synthetic leather case for vernier calipers	412500
Table for calipers	412180