

Waldmann **LED rectangular lamp magnifier without stand, Type: 2****Order data**

Order number	491521 2
GTIN	4013330089412
Item class	49A

Description**Version:**

LED lamp magnifier for anti-glare and evenly illuminated work field. Freely moving jointed arm. The spring holds the lamp in any position.

- **Hardened, ground and scratch-resistant glass lens. Pivoting.**
- **Rectangular magnifying glass lamp for powerful and even illumination over a large area, with 54 LEDs. Power consumption only 12 W, light intensity 6000 Lx, multi-stage switchable. LEDs up to 50,000 h working life.**
- **Segment switching for recognition of the finest structures and errors. Depending on the application can be switched between light with formation of shadows and all-round shadow-free light.**
- **Large field of view for distortion-free viewing.**

Supplied with:

With cover and plastic screw-on foot.

Optional extras:

Table base No. 491660, table clamp No. 491670.

Note:

The light source can be exchanged by the manufacturer.

Technical description

Head dimensions width	194 mm
Lens width	105 mm
Head dimensions height	75 mm
Throat	900 mm
Weight	2 kg
Lens length	162 mm
Head dimensions length	298 mm
Magnification (x-times)	1.75
Power supply	Mains operated
Bulb	LED module
Lamp replaceable	no
Type of product	Magnifying glass lamp

Accessories

Table base for magnifying glass lamp No. 491521	491660
-------------------------------------------------	--------