



## Modular vice, Jaw width A: 200/4mm



### Order data

Order number	362100 200/4
GTIN	2050001719539
Item class	35G

### Description

#### Version:

- Simple mechanical actuation (up to 3.5 t).
- Easy adjustment of jaw opening.
- Machine vice with pull-down jaws.
- Case-hardened HRC 60.
- Parallelism 0.02 mm.

#### Supplied with:

Supplied with pull-down jaws, 1 workpiece backstop, 2 T-nuts No. 362160 size 16/16, 1 clamping wrench, 1 cross-bar wrench.

#### Note:

For other T-nuts see No. 362160.

### Technical description

Jaw width A	200 mm
Clamping range b	400 mm
Weight	74 kg
Longitudinal tenon slot l	16 mm
Jaw height C	65 mm
Transverse tenon slot n	16 mm

Colour code for suitable accessories	Gerardi 200
Overall length L	695 mm
Base body height G	70 mm
maximum clamping force at 120 Nm	40 kN
Series	Gerardi 200
Type of product	Machine vice

## Accessories

Pair of T-nuts T-slot dimension B / keyway 12/16 mm	362160 12/16
Pair of T-nuts T-slot dimension B / keyway 16/16 mm	362160 16/16
Pair of clamps for jaw width 200 mm	362120 200
Pair of T-nuts T-slot dimension B / keyway 18/16 mm	362160 18/16
Pair of T-nuts T-slot dimension B / keyway 14/16 mm	362160 14/16
Longitudinally serrated front jaw (piece) for jaw width 200 mm	362146 200
Smooth front jaw, hard (piece) for jaw width 200 mm	362147 200
Pair of T-nuts T-slot dimension B / keyway 20/16 mm	362160 20/16
Smooth front jaw, soft (piece) for jaw width 200 mm	362148 200