

**Teroson**
**Teromix 2-component PU adhesive, 50 ml, Manufacturer ID: 6700ME**

**Order data**

Order number	083378 6700ME
GTIN	4002872012453
Item class	04L

**Description**
**Version:**

Universal adhesive. For bonding many different materials such as stainless steel, aluminium and other metals, plastics, wood and painted surfaces (not recommended for PP and PE). Curing is independent of temperature and humidity. Easy to apply using the static mixer supplied.

Labelling of hazardous substances: GHS07 Caution

Contents: 50 ml

Processing period: 30 min

Tensile shear strength: 13 N/mm<sup>2</sup>

**Technical description**

Labelling of hazardous substances	GHS07 Caution
Tensile shear strength	13 N/mm <sup>2</sup>
Manufacturer's designation	PU 6700 ME
Dynamic viscosity	16000 mPas
Shape	Paste

Chemical basis	Polyurethane
Suitable for application area	Repairs
Colour	grey
Characteristics	can be ground
Hardness according to Shore A	95
Storage temperature	10 °C
Operating temperature range	-40 °C
Working life after date of manufacture	12 month
Processing time	5 s
Capacity	50 g
Processing temperature	18 - 25 °C
Suitable for material	Stainless steel (INOX)
Suitable for material	Aluminium
Suitable for material	Plastic
Suitable for material	wood
Density	1.45 g/cm <sup>3</sup>
Functional strength to	5 min
Touch dry after	2 min
Maximum gap size	3 mm
Product name attribute	50 ml
Type of product	Two-component adhesive