

Garant

GARANT Master Steel FEED solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 15,5



Order data

Order number	123035 15,5
GTIN	4045197840035
Item class	11E

Description

Version:

3-flute drill, specially developed for **use at very high feed rates**. Outstandingly suitable for **machines with high installed power** and stable operating conditions.

- **Special cutter geometry with stable cutting edges and large clearance at the centre enables very high feed rates.**
- **The patented tip is optimised for chip flow and generates low cutting pressure with good chip breakage.**

The **sector-leading technology of the drill point** guarantees **optimum self-centring behaviour**. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 123036**.

Form **HE**: order with **No. 123035 + 129100HE**.

Standard: Manufacturer's standard

Tolerance nominal Ø: h7

Number of cutting edges Z: 3

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 128.8 mm

Overall length L: 203 mm

Shank Ø D_s : 16 mm

Feed f in steel < 1100 N/mm²: 0.61 mm/rev.

Technical description

Overall length L	203 mm
Feed f in steel < 1100 N/mm ²	0.61 mm/rev.
Flute length L _c	152 mm
Shank Ø D _s	16 mm
Standard	Manufacturer's standard
recommended maximum drilling depth L ₂	128.8 mm
Nominal Ø D _c	15.5 mm
Number of cutting edges Z	3
Tolerance nominal Ø	h7
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Version	8×D
Point angle	140°
Shank	DIN 6535 HA to h6
Through-coolant	yes, to 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	110 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	70 m/min	P
Steel < 55 HRC	suitable	60 m/min	H

INOX < 900 N/mm ²	suitable	55 m/min	M
INOX > 900 N/mm ²	suitable	50 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG	suitable	120 m/min	K
GGG	suitable	80 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Services			

Shank grinding Type HE

129100 HE