

PLANOLITH
Granite plate Accuracy class 0, Length×Width: 400X400mm

Order data

Order number	430300 400X400
GTIN	2050001040671
Item class	46H

Description
Version:

Specially selected natural granite.

- **Free from defects, homogeneous structure.**
- **Resistant to deflection and to warping.**
- **Absolutely rust-proof and acid resistant, low thermal conductivity.**
- **Micro-fine machine surface (diamond lapped). Within all the permissible tolerances.**
- **Ground outside edges, visually true.**
- **For mounting as determined statically, contact points (steel ball inserts) are fitted to the underside.**
- **Harder than hardened steel (Mohs hardness scale 6 – 7), non-magnetic and electrically non-conductive.**

Accuracy:

Final manufacturing and inspection take place in computer-controlled climatic rooms. The used measuring equipment guarantees the exact connection to national and international calibration laboratories.

DIN 876/0 – Precision diamond lapped for inspection.

Supplied with:

Supplied with test certificate, transport packing. Including rubber feet.

Note:

On request: Stainless steel screw inserts, steel T-slot rails (steel T-slot rails not available for No. 430190), accuracy 000, other sizes, intermediate sizes. Delivery excluded.

Technical description

Weight	25 kg
Thickness	50 mm

Flatness	0.006 mm
Number of rubber feet	4
Standard	DIN 876
Accuracy	0 mm
Test certificate	Manufacturer's test certificate
Type of product	Graduated plate