

**Internal micrometer, Measuring range: 75-100mm****Order data**

Order number	426800 75-100
GTIN	4045197204158
Item class	42B

Description**Version:**

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

Supplied with:

Supplied with setting ring for adjustment.

Technical description

Barrel Ø	18 mm
Measuring range	75 - 100 mm
Scale divisions	0.01 mm
Error limit	16 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Calibration	L7
Type of product	Internal micrometer

Services

DAkkS calibrationSetting ring maximum \varnothing 200 mm	028470 200
CalibrationSetting ring maximum \varnothing 100 mm	028400 100
CalibrationInternal micrometer maximum measuring range 100 mm	022360 100

Accessories

Setting ringDIN 2250 C Nominal size \varnothing 80 mm	484030 80
Setting ringDIN 2250 C Nominal size \varnothing 90 mm	484030 90
Setting ringDIN 2250 C Nominal size \varnothing 100 mm	484030 100