



## HOLEX Pro Steel solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 1,6



### Order data

Order number	122776 1,6
GTIN	4045197826930
Item class	12F

### Description

#### Version:

**Straight major cutting edges** and a **special flute profile** ensure a good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and an extremely wear-resistant coating.

Up to Ø 1.9 with 4 facets, from Ø 2 with relieved cone.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Versions with HB and HE shank available at the same price as HA.

For **HB shanks**: use order **no. 122777**.

For **HE shanks**: use order **No. 122778**.

Standard: DIN 6537

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

recommended maximum drilling depth  $L_2$ : 10.6 mm

Overall length L: 50 mm

Shank Ø  $D_s$ : 4 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.05 mm/rev.

### Technical description

recommended maximum drilling depth $L_2$	10.6 mm
Flute length $L_c$	13 mm
Tolerance nominal Ø	h7

Standard	DIN 6537
Shank $\varnothing D_s$	4 mm
Feed $f$ in steel $< 900 \text{ N/mm}^2$	0.05 mm/rev.
Number of cutting edges $Z$	2
Overall length $L$	50 mm
Nominal $\varnothing D_c$	1.6 mm
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	140 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions	160 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	125 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	115 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	95 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	90 m/min	P

Steel < 1400 N/mm <sup>2</sup>	suitable	65 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	M
GG	suitable	100 m/min	K
GGG	suitable	65 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		