

Garant**Centring vice, Jaw width A: 80mm****Order data**

Order number	360130 80
GTIN	4045197642387
Item class	310

Description**Version:**

Centring vice for flexible applications.

- **Absolute operational reliability thanks to enclosure.**
- **High repetition accuracy 0.02 mm.**
- **Variable central alignment ± 0.02 mm.**
- **Functional faces hardened.**
- **Sturdy design of tool steel, surface protection by brief exposure nitriding.**

Advantage:

Multi-functional uses.

- **Flexible lightweight.**

Application:

Ideal for 5-face machining, perfect for clamping blank parts.

Suitable for:

Multi-point clamping rails No. 360080 and 360110.

Supplied with:

Supplied with socket No. 642700 size E12.

Optional extras:

Types of jaws No. 360135– 360151.

Technical description

Length	110 mm
Weight	2.5 kg
Stroke	22 mm
Torque	40 Nm
Height	50.2 mm
Jaw width A	80 mm
Clamping force up to maximum	17 kN
Width	80 mm
suitable for colour code	ZC 80
Type of product	Machine vice

Accessories

Pair of gripp top jaws for type 80	360141 80
Centring/adapter plate Type T2	360132 T2
Clamping stud for centring vice Type 18M12/120	360131 18M12/120
Pair of gripp top jaws for type 80	360142 80
Pair of carbide top jaws for type 80	360137 80
Clamping stud for centring vice Type 18M12/138	360131 18M12/138
Pair of gripp top jaws for type 80	360140 80
Pair of carbide top jaws for type 80	360138 80
Centring/adapter plate Type T1	360132 T1
Pair of carbide top jaws for type 80	360135 80
Pair of gripp top jaws for type 80	360143 80
Pair of soft top jaws for type 80	360146 80
Pair of carbide top jaws for type 80	360136 80
Pair of Vee jaws for type 80	360148 80
Pair of soft top jaws for type 80	360145 80
Extension base for centring vice for type 80	360152 80

