

**Garant**
**GARANT Master Steel FEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 15,8mm**

**Order data**

Order number	123236 15,8
GTIN	4045197843401
Item class	11E

**Description**
**Version:**

**3-flute drill**, specially developed for **use at very high feed rates**. Outstandingly suitable for machines with **high installed power** and stable machining conditions.

- **Special cutter geometry with stable cutting edges and large clearance at the centre enables very high feed rates.**
- **The patented tip is optimised for chip flow and generates low cutting pressure with good chip breakage.**

The **sector-leading technology of the drill point** guarantees **optimum self-centring behaviour**. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For process reliability when using the 12xD deep-hole drill, an initial centre drilling with an NC spotting drill No. 121130 with **155° point angle** is necessary.

**Technical description**

Standard	Manufacturer's standard
recommended maximum drilling depth $L_2$	184.3 mm
Tolerance nominal Ø	h7
Flute length $L_c$	208 mm
Shank Ø $D_s$	16 mm
Nominal Ø $D_c$	15.8 mm

Number of cutting edges Z	3
Overall length L	260 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.61 mm/rev.
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Version	12xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, to 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 55 HRC	suitable	60 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	55 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	S
GG	suitable	120 m/min	K
GGG	suitable	80 m/min	K

Uni	suitable
wet maximum	suitable
wet minimum	suitable