


CNMG 120412, Grade: PV720

Order data

Order number	250214 PV720
GTIN	4960664723614
Item class	25E

Technical description

Grade	PV720
Cutting depth a_p	1 - 3.5 mm
Cutting speed v_c main application	110 - 490 m/min
Chip breaker	PG
Feed f	0.15 - 0.35 mm/rev.
Cutting conditions	continuous
Main application	P
Corner radius	1.2 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	CNMG 120412
Number of changes/inserts	4

Type of product

Indexable insert for turning