


**DNMG 150604, Grade: PV720**

**Order data**

Order number	250796 PV720
GTIN	4960664724604
Item class	25E

**Technical description**

Corner radius	0.4 mm
Feed f	0.15 - 0.6 mm/rev.
Cutting speed $v_c$ main application	110 - 490 m/min
Main application	P
Cutting conditions	continuous
Chip breaker	PG
Grade	PV720
Cutting depth $a_p$	1 - 4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	DNMG 150604
Number of changes/inserts	4

Type of product

Indexable insert for turning