


**DNMG 150612, Grade: PV720**

**Order data**

Order number	250798 PV720
GTIN	4960664724628
Item class	25E

**Technical description**

Main application	P
Cutting conditions	continuous
Feed f	0.15 - 0.6 mm/rev.
Chip breaker	PG
Grade	PV720
Corner radius	1.2 mm
Cutting speed $v_c$ main application	110 - 490 m/min
Cutting depth $a_p$	1 - 4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	DNMG 150612
Number of changes/inserts	4

Type of product

Indexable insert for turning