


TNMG 160408, Grade: PV720

Order data

Order number	251583 PV720
GTIN	4960664725434
Item class	25E

Technical description

Corner radius	0.8 mm
Main application	P
Cutting depth a_p	1 - 4.5 mm
Feed f	0.15 - 0.6 mm/rev.
Chip breaker	PG
Cutting conditions	continuous
Cutting speed v_c main application	110 - 490 m/min
Grade	PV720
Finishing/roughing assignment	Semi-roughing
Tool material	Cermet
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6

Type of product

Indexable insert for turning