


DNMG 150604, Grade: PV720

Order data

Order number	250696 PV720
GTIN	4960664724574
Item class	25E

Technical description

Cutting speed v_c main application	110 - 520 m/min
Cutting depth a_p	0.2 - 2.5 mm
Chip breaker	PQ
Main application	P
Cutting conditions	continuous
Corner radius	0.4 mm
Feed f	0.05 - 0.3 mm/rev.
Grade	PV720
Finishing/roughing assignment	Finishing
Tool material	Cermet
ISO code indexable insert	DNMG 150604
Number of changes/inserts	4

Type of product

Indexable insert for turning