


DNMG 150608, Grade: PV720

Order data

Order number	250697 PV720
GTIN	4960664724581
Item class	25E

Technical description

Cutting conditions	continuous
Cutting depth a_p	0.2 - 2.5 mm
Grade	PV720
Cutting speed v_c main application	110 - 520 m/min
Corner radius	0.8 mm
Feed f	0.05 - 0.3 mm/rev.
Chip breaker	PQ
Main application	P
Finishing/roughing assignment	Finishing
Tool material	Cermet
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4

Type of product

Indexable insert for turning