

**CC.T 060202, Grade: PV720**

Order data

Order number	260192 PV720
GTIN	4960664726905
Item class	25E

Technical description

Main application	P
Cutting depth a_p	0.5 - 3 mm
Chip breaker	GK
Corner radius	0.4 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting conditions	continuous
Grade	PV720
Cutting speed v_c main application	60 - 270 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	CCMT 060204
Number of changes/inserts	2

Tolerance	M
Type of product	Indexable insert for turning