


CC.T 09T304, Grade: PV720

Order data

Order number	260196 PV720
GTIN	4960664726912
Item class	25E

Technical description

Cutting speed v_c main application	60 - 270 m/min
Corner radius	0.4 mm
Grade	PV720
Cutting depth a_p	0.5 - 3 mm
Main application	P
Feed f	0.1 - 0.3 mm/rev.
Chip breaker	GK
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Cermet
ISO code indexable insert	CCMT 09T304
Number of changes/inserts	2

Tolerance	M
Type of product	Indexable insert for turning