


DC.T 11T304, Grade: PV720

Order data

Order number	260386 PV720
GTIN	4960664724154
Item class	25E

Technical description

Cutting speed v_c main application	60 - 270 m/min
Cutting depth a_p	0.5 - 1.5 mm
Cutting conditions	continuous
Grade	PV720
Chip breaker	HQ
Corner radius	0.4 mm
Main application	P
Feed f	0.05 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Cermet
ISO code indexable insert	DCMT 11T304
Number of changes/inserts	2

Tolerance	M
Type of product	Indexable insert for turning