



## XT internal micrometer set, Measuring range: 100-150mm



### Order data

Order number	428550 100-150
GTIN	5051102033293
Item class	46B

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate.

#### Application:

Blind holes and through holes, centring edges.

#### Supplied with:

Internal micrometers No. 428500 and setting rings with UKAS test certificate.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

### Technical description

Measuring range	100 - 150 mm
Setting ring $\varnothing$	125 mm
Number of micrometers	2
Number of setting rings	1

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

### Services

CalibrationInternal micrometer set Measuring range 100-150 mm	020550 100-150
---------------------------------------------------------------	----------------

### Accessories

XT internal micrometer Measuring range 100-125 mm	428500 100-125
Setting ringDIN 2250 C Nominal size Ø 130 mm	484030 130
Extension for internal micrometers Type 5/150	428510 5/150
XT internal micrometer Measuring range 125-150 mm	428500 125-150
Replacement XT measuring head Measuring range 100-125 mm	428605 100-125
Setting ringDIN 2250 C Nominal size Ø 110 mm	484030 110