



## XT internal micrometer, Measuring range: 50-65mm



### Order data

Order number	428500 50-65
GTIN	5051102095819
Item class	46B

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. For blind hole measurements from size 12.5 – 16. Internal micrometers for maximum precision. Fixed carbide measuring jaws, from size 12.5 with carbide inserts.

#### Application:

Blind holes and through holes, centring edges.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

### Technical description

Measuring depth with extension	230 mm
Dimension a	0.5 mm
Measuring range	50 - 65 mm

Standard measuring depth	80 mm
Error limit	0.005 mm
Scale divisions	0.005 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 100 mm	022500 100

## Accessories

Setting ring DIN 2250 C Nominal size $\varnothing$ 55 mm	484030 55
Replacement XT measuring head Measuring range 50-65 mm	428605 50-65
Setting ring DIN 2250 C Nominal size $\varnothing$ 50 mm	484030 50
Setting ring DIN 2250 C Nominal size $\varnothing$ 65 mm	484030 65
Setting ring DIN 2250 C Nominal size $\varnothing$ 60 mm	484030 60
Extension for internal micrometers Type 5/150	428510 5/150
Measuring jaws set 3 pieces Measuring range 50-65 mm	428745 50-65
Return spring set 3 pieces Measuring range 50-65 mm	428746 50-65