



Heavy push-pull toggle clamp, Type: 3



Order data

Order number	376720 3
GTIN	4020772094232
Item class	35A

Description

Version:

- **Very sturdy design, with slide-ram guide.**
- **Slide-ram and hand lever move together.**
- **Body of malleable cast iron.**
- **Lever parts and slide ram made of quenched and tempered steel, galvanised and passivated.**
- **Hardened contact screw.**

Application:

- **For quick clamping / releasing in series production.**
- **As push or pull clamp.**
- **For incorporation within special jigs and fixtures.**
- **Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.**

Technical description

Hole spacing e	41 mm
Clamping height b to centre of screw	30 mm
Clamping force P (pressure and traction)	4000 N
Bore \varnothing d	6.5 mm

Contact screw	M8×35 mm
Hole spacing g	36 mm
Hole spacing f	44 mm
Clamping range	32 mm
Overall height H	116 mm
Overall length L	309 mm
Type	6842
Type of product	Push-pull toggle clamp