



Digital XTL internal quick measuring set, Measuring range: 20-50mm



Order data

Order number	428770 20-50
GTIN	5051102120542
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- mm / inch selection.
- Setting 2 preset values.
- On / Off data storage button.

Supplied with:

Digital internal micrometers No. 428760 and setting rings with UKAS test certificate.

Technical description

Number of measuring heads	3
Setting ring \varnothing	20 / 35 mm
Measuring range	20 - 50 mm
Error limit	0.004 mm

Scale divisions	0.001 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

Services

CalibrationInternal micrometer set Measuring range 20-50 mm	020550 20-50
---	--------------

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Setting ringDIN 2250 C Nominal size Ø 30 mm	484030 30
Extension for internal micrometers Type 4/150	428510 4/150
Receiver / USB keyboard interface Type	498965
Connection cable Duplex Type 2	498950 2
Connection cable Duplex Type USB2	498950 USB2
Setting ringDIN 2250 C Nominal size Ø 40 mm	484030 40
Multi-receiver / USB keyboard interface Type	498975
Setting ringDIN 2250 C Nominal size Ø 22 mm	484030 22