

Garant**Deep hole drill HSS-E, uncoated, Ø DC h8: 1,4mm****Order data**

Order number	116061 1,4
GTIN	4045197026521
Item class	11B

Description**Version:**

Significantly **strengthened core** without taper.

Precision ground point.

With **specially shaped slots**. Designed for deep holes up to 10×D and materials with critical chip formation characteristics.

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability.

Technical description

Flute length L_c	45 mm
Feed f in steel < 500 N/mm ²	0.05 mm/rev.
Nominal Ø D_c	1.4 mm
Number of cutting edges Z	2
Tolerance nominal Ø	h8
Shank Ø D_s	1.4 mm
Overall length L	70 mm
Standard	DIN 340
recommended maximum drilling depth L_2	42.9 mm

Point angle	130 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	FS
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	45 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable	21 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable	25 m/min	K
Oil	suitable		
wet maximum	suitable		