



Digital XTL internal quick measuring set, Measuring range: 50-100mm



Order data

Order number	428770 50-100
GTIN	5051102120559
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Digital internal micrometers No. 428760 and setting rings with UKAS test certificate.

Technical description

Setting ring \varnothing	65 / 80 mm
Number of measuring heads	3
Measuring range	50 - 100 mm
Error limit	0.005 mm

Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

Services

CalibrationInternal micrometer set Measuring range 50-100 mm	020550 50-100
---	---------------

Accessories

Connection cable Duplex Type 2	498950 2
Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965
Setting ringDIN 2250 C Nominal size Ø 60 mm	484030 60
Setting ringDIN 2250 C Nominal size Ø 90 mm	484030 90
Setting ringDIN 2250 C Nominal size Ø 75 mm	484030 75
Extension for internal micrometers Type 5/150	428510 5/150
Connection cable Duplex Type USB2	498950 USB2
Button cell / special battery Battery type CR2032	081560 CR2032