

Garant

**Side lock arbor Form ADB with cooling channel bores, SK 50 A = 160,
Clamping range \varnothing D1: 32mm**


Order data

| | |
|--------------|---------------|
| Order number | 300351 32 |
| GTIN | 4045197830128 |
| Item class | 31A |

Description
Version:
GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

With coolant supply holes that can be plugged.

With Balluff/RFID chip bore.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|---------------|
| External \varnothing D | 72 mm |
| Overhang dimension A | 160 mm |
| Spare clamping screw No. 30 9900 | 32 |
| Clamping \varnothing D ₁ | 32 mm |
| Adapter | SK 50 A = 160 |
| Standard | DIN 6359 |
| Arbor standard | ISO 7388-1 |
| Shape | ADB |

| | |
|---------------------------------------|---------------------|
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 3 μm |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|---|-----------|
| Pull studForm A suitable for steep tapers 50 | 308600 50 |
| Pull studsealed, form B suitable for steep tapers 50 | 308620 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308795 50 |
| Pull studForm B suitable for steep tapers 50 | 308640 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308790 50 |
| Special pull stud with no internal threadsealed suitable for steep tapers 50 | 308720 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308760 50 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50 | 308820 50 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50 | 308615 50 |
| Pull studsealed, form B suitable for steep tapers 50 | 308650 50 |
| Pull stud 60°sealed suitable for steep tapers 50 | 308785 50 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 50 | 308830 50 |
| Special pull stud with internal thread suitable for steep tapers 50 | 308740 50 |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 50 | 308605 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308765 50 |
| Pull studsealed, form A suitable for steep tapers 50 | 308610 50 |
| Pull studsealed suitable for steep tapers 50 | 308660 50 |
| Spare clamping screw for chucks with clamping Ø D1 32 mm | 309900 32 |